

1. 產品規格


規格	5Pm2.5
規格	PM2.5
規格	規格+規格+規格+規格
規格	規格17.5 * 12.4cm 規格23.5 * 13.6cm 規格24.7 * 16cm
規格	11/
規格	規格
規格	規格PM2.5
規格	規格PM2.5規格
規格	10-30
規格	1/規格
規格	規格
規格	10000











Insert PM2.5 air particles
through the filter into the
interlayer

Cover your nose and mouth
and hang the rubber bands
on your ears


Fix the nose clip to the
nose

5-layer meltblown cloth filter





Fiber diameter of meltblown cloth reaches 1-5 microns, effectively filtering Pm2.5, pollutants and droplets



Test Report

Haze particle barrier test:
KP 10 > 99.97%

AL MA CNAS No. 2014 (全) -098

检验报告

产品名称: PM2.5口罩
委托单位: 安佑防护用品公司
检验类别: 委托

国家劳动防护用品质量监督检验中心 (北京)

Test air flow:
Single filter element(84+4)L/min

检验结果汇总

序号	检测项目	检测结果	标准要求	备注
1	初始过滤效率	99.6%	≥99.5%	合格
2	加载后过滤效率	99.97%	≥99.5%	合格
3	初始过滤效率	99.6%	≥99.5%	合格
4	加载后过滤效率	99.96%	≥99.5%	合格
5	初始过滤效率	99.6%	≥99.5%	合格
6	加载后过滤效率	99.98%	≥99.5%	合格
7	初始过滤效率	99.5%	≥99.5%	合格
8	加载后过滤效率	99.95%	≥99.5%	合格
9	初始过滤效率	99.5%	≥99.5%	合格
10	加载后过滤效率	99.97%	≥99.5%	合格
11	初始过滤效率	99.6%	≥99.5%	合格
12	加载后过滤效率	99.97%	≥99.5%	合格
13	初始过滤效率	99.4%	≥99.5%	合格
14	加载后过滤效率	99.95%	≥99.5%	合格
15	初始过滤效率	99.6%	≥99.5%	合格
16	加载后过滤效率	99.96%	≥99.5%	合格
17	初始过滤效率	99.5%	≥99.5%	合格
18	加载后过滤效率	99.97%	≥99.5%	合格
19	初始过滤效率	99.6%	≥99.5%	合格
20	加载后过滤效率	99.96%	≥99.5%	合格

检测日期: 2014年10月10日
检测地点: 国家劳动防护用品质量监督检验中心 (北京)

*Filter test report



A diagram of a 4-bit shift register. It consists of four rectangular blocks representing flip-flops, arranged horizontally. Each block has a label below it: Q3, Q2, Q1, and Q0 from left to right. The blocks are connected in a chain, with the output of one flip-flop connected to the input of the next. The entire register is shown above a horizontal line representing the data bus.



A horizontal row of 7 rectangular boxes, each representing a slot in a queue. The first 6 boxes are filled with a solid black color, and the 7th box is empty. A horizontal line extends from the right side of the 7th box.



□□□□□□□□□□ □□□□□□ □□ □□□□□□□□ ^^

□□□□□□□□□□ □□□□□□ □□ □□□□□□□□ ^^